

## MOUSE JIGGLER™ QUICK START GUIDE

(Revised March 29, 2011)



### Features

- **Easy to use** – Plug-and-Play! No cables, drivers, or software are needed. Just plug it in and Mouse Jiggler will immediately start to work.
- **Very Portable** – Mouse Jiggler is about the size of a car key and is every bit as portable.
- **No More Screen Savers** – Mouse Jiggler prevents screen saver and sleep modes by jiggling the mouse pointer.
- **Widely Compatible** – Works with Windows, Mac OS, and HID compliant operating systems.
- **Two versions** – Pick the model that's best for you. MJ-1 (black case) moves the mouse pointer slowly so you can use the computer while it works. MJ-2 (blue case) moves the mouse pointer very quickly so you can see at a glance that it's working.

### Operation

**Step One:** Plug Mouse Jiggler into a USB port on any computer.

That's it! Sit back and watch Mouse Jiggler disable screen saver and sleep modes by automatically moving the mouse pointer at regular intervals. With standard Jiggler (MJ-1), you can continue to use the computer while Mouse Jiggler is doing its job. Remove Mouse Jiggler from the USB port and your screen saver settings and sleep mode will be enabled.

Note: you can easily tell how long Mouse Jiggler has been working by watching its LED. The repeating blink pattern represents a four digit number indicating how many minutes have passed. Each digit is shown as a succession of 1 to 10 blinks, indicating the digits 0-9. Simply subtract one from the number of blinks to get the correct digit. For example, the pattern [1 blink, 1 blink, 3 blinks, 8 blinks] represents [0, 0, 2, 7], or 27 minutes.

### Technical Specifications

<b>Product name &amp; Code</b>	Mouse Jiggler (MJ-1, MJ-2)
<b>Data Interfaces</b>	USB 1.1/2.0
<b>Hot-Swappable</b>	Yes
<b>Operating System</b>	Windows, Mac OS - HID Compliant Operating Systems
<b>Shipping Weight</b>	1 lb.
<b>Dimensions</b>	(38mm Length x 12mm Width x 6.35mm Depth)
<b>Operating Temperature</b>	50° – 85° F (10° – 30° C)
<b>Operating Humidity</b>	5% - 85%, noncondensing
<b>Warranty</b>	1-year limited warranty. See warranty statement for details and limitations. WiebeTech offers 90 days of free phone support (1-866-744-8722). After 90 days, email support is available at <a href="mailto:support@wiebetech.com">support@wiebetech.com</a> .